


























NO.	Dimensions (length+width+height+thickness) (mm)	picture	Model	material quality	barb	Card blade thickness (mm)	Salt spray test (h)
1	10*3.6*2.2*0.2		0.05g	65Mn	Single sided	0.5-1.8	240
2	7.8*2.6*2.0*0.2		0.05gE	SUS304	Single sided	0.5-1.8	96
3	7.6*2.6*2.2*0.2		0.05gF	SUS304	Single sided	1-1.8	96
4	6x4x2x0.2		0.06g	65Mn	Single sided	0.5-1.5	240
5	6x4x2x0.2		0.08g	65Mn	Single sided	0.5-1.5	240
6	7.6*4.2*2.5*0.2		0.1gS	SUS304	two-sided	0.5-2.0	96
7	7.9*2.9*2.0*0.3		0.1gE	SUS304	Single sided	0.5-1.8	96
8	7.9*2.9*2.0*0.3		0.1gF	SUS304	Single sided	1-1.8	96
9	10.8*3.5*2.2*0.2		0.1gA	65Mn	Single sided	0.5-1.8	240
10	11.1*3.5*2*0.2		0.1gB	65Mn	Single sided	0.5-1.8	240
11	9.6*5*2*0.2		0.15gE	SUS304	Single sided	0.5-1.8	96
12	9.6*5*2.2*0.2		0.15gF	SUS304	Single sided	1-1.8	96
13	8.6*6*2.8*0.2		0.15gS	SUS304	two-sided	0.5-2.5	96
14	9.6*5*2*0.2		0.15gB	65Mn	Single sided	0.5-1.8	240
15	9.6*5*2.3*0.3		0.2gE	SUS304	Single sided	0.5-1.8	96

NO.	Dimensions (length+width+height+thickness) (mm)	picture	Model	material quality	barb	Card blade thickness (mm)	Salt spray test (h)
16	9.6*5*2.5*0.3		0.2gF	SUS304	Single sided	1-2	96
17	8.6*6*2.8*0.3		0.2gS	SUS304	two-sided	0.5-2.0	96
18	10.8*4.1*3*0.3		0.2gA	65Mn	Single sided	0.5-2.5	240
19	11.9*4.1*2.0*0.3		0.2gB	65Mn	Single sided	0.5-1.8	240
20	5.3*5.6*1.7*0.3		0.2gC	65Mn	Single sided	0.5-1.2	240
21	5.7*10*2.9*0.3		0.25gC	65Mn	two-sided	1.5-2.5	240
22	10.5*5*2.7*0.35		0.25gE	SUS304	Single sided	1-2.2	96
23	10.4*5*3*0.4		0.3gE	65Mn	Single sided	0.5-2.5	240
24	10.4*5*3.2*0.4		0.3gF	65Mn	Single sided	1-2.5	240
25	10.5*5*2.6*0.4		0.3gE	SUS304	Single sided	0.5-2.0	96
26	10.5*5*3.2*0.4		0.3gF	SUS304	Single sided	1-2.5	96
27	8.8*7.2*3.4*0.3		0.3gS	SUS304	two-sided	0.5-2.8	96
28	10.4*5*3*0.4		0.3gB	65Mn	Single sided	0.5-2.5	240
29	10*5.4*3.2*0.4		0.35g	65Mn	Single sided	1-2.5	240
30	9.7*10.2*3.0*0.3		0.4g	65Mn	two-sided	1-2.5	240

NO.	Dimensions (length+width+height+thickness) (mm)	picture	Model	material quality	barb	Card blade thickness (mm)	Salt spray test (h)
31	11*5*2.9*0.5		0.4gE	SUS304	Single sided	1-2.0	96
32	11*5*3*0.5		0.4gF	SUS304	Single sided	1.5-2.5	96
33	9.7*10.2*3*0.3		0.4gE	SUS304	two-sided	0.8-2.5	96
34	9.7*10.2*3.1*0.3		0.4gF	SUS304	two-sided	1.2-2.5	96
35	11*5*2.9*0.5		0.4gB	65Mn	Single sided	1-2.0	240
36	12*6*3.2*0.5		0.5gE	SUS304	Single sided	0.8-2.5	96
37	12*6*3.5*0.5		0.5gF	SUS304	Single sided	2-3	96
38	11.5*8*2.5*0.35		0.5gD	SUS304	Single sided	0.8-2.2	96
39	14.5*6.6*4.7*0.5		0.5gL	65Mn	Single sided	1.5-4.0	240
40	12*6.1*3.5*0.5		0.5gX	65Mn	Single sided	1.0-2.5	240
41	10.4*10.2*3.0*0.4		0.6gE	65Mn	two-sided	0.8-2.2	240
42	10.4*10.2*3.2*0.4		0.6gE	65Mn	two-sided	1-2.2	240
43	10.4*10.2*3.0*0.4		0.6gF	SUS304	two-sided	0.8-2.2	96
44	14.3*8*3.25*0.4		0.7gE	65Mn	Single sided	0.5-2.5	240
45	14.3*8*3.25*0.4		0.7gF	65Mn	Single sided	1.5-2.5	240

NO.	Dimensions (length+width+height+thickness) (mm)	picture	Model	material quality	barb	Card blade thickness (mm)	Salt spray test (h)
46	10.7*10.2*3.9*0.5		0.8gE	65Mn	two-sided	1-3.0	240
47	10.7*10.3*4.3*0.5		0.8gF	65Mn	two-sided	1.5-3.0	240
48	10.7*10.3*4*0.5		0.8gF	SUS304	two-sided	1-3.0	96
49	10.7*10.3*4.3*0.5		0.8gE	SUS304	two-sided	1.5-3.0	96
50	12.2*10*3.1*0.4		0.8gD	SUS304	Single sided	1.5-2.5	96
51	15.4*8.4*3.6*0.6		1.0gE	65Mn	Single sided	1-2.2	240
52	15.4*8.4*3.8*0.6		1.0gF	65Mn	Single sided	1.5-2.5	240
53	15.4*8.4*3.2*0.6		1.0gE	SUS304	Single sided	0.8-2.0	96
54	15.2*8.4*3.5*0.6		1.0gF	SUS304	Single sided	1.5-2.2	96
55	13.7*13*4*0.4		1.0gF	SUS304	two-sided	1.5-3.2	96
56	13.7*13*4.2*0.5		1.3gE	SUS304	two-sided	1-3.0	96
57	13.7*13*4.4*0.5		1.3gF	SUS304	two-sided	2-3.4	96
58	13*13*5.5*0.5		1.4g	SUS304	two-sided	3-4.5	96
59	16*11*3.7*0.6		1.5gE	65Mn	Single sided	0.8-2.5	240
60	16*11*4.1*0.6		1.5gF	65Mn	Single sided	1.8-3.0	240

NO.	Dimensions (length+width+height+thickness) (mm)	picture	Model	material quality	barb	Card blade thickness (mm)	Salt spray test (h)
61	16.2*11*3.5*0.6		1.5gE	SUS304	Single sided	0.8-2.2	96
62	16.2*11*4.0*0.8		2.0gE	65Mn	Single sided	0.8-2.5	240
63	16.2*11*4.5*0.8		2.0gF	65Mn	Single sided	1.8-3.0	240
64	16*6.5*7.4*1.3		2.0gZ	65Mn	Single sided	3.5-4.8	240
65	16.4*11*3.8*0.8		2.0gE	SUS304	Single sided	0.8-2.2	96
66	16.4*11*4.2*0.8		2.0gF	SUS304	Single sided	2.0-3.5	96
67	17.8*19.3*3.8*0.5		2.5gE	65Mn	Single sided	2.0-3.0	240
68	17.8*19.3*3.8*0.5		2.5gE	SUS304	Single sided	2.0-3.0	96
69	17.7*18.7*4*0.6		3.0gE	65Mn	Single sided	0.8-3.0	240
70	17.5*18.7*4.2*0.6		3.0gE	65Mn	Single sided	1.2-3.0	240
71	16*8.4*7.4*1.5		3.0gZ	65Mn	Single sided	3.8-4.8	240
72	18.1*6.4*10*1.6		3.0gZR	65Mn	Single sided	6-7	240
73	17.7*18.7*3.8*0.6		3.0gE	SUS304	Single sided	0.8-2.5	96
74	17.7*18.7*4.0*0.6		3.0gF	SUS304	Single sided	2.0-3.0	96
75	14.7*8.7*8.5*1.5		3.0gW	SUS304	two-sided	3.8-5.5	96

NO.	Dimensions (length+width+height+thickness) (mm)	picture	Model	material quality	barb	Card blade thickness (mm)	Salt spray test (h)
76	17.5*18.7*8.5*1.5		4.0g	SUS304	Single sided	1.6-3.0	96
77	18.1*8.5*10*1.6		4.0gZ	65Mn	Single sided	6-7	240
78	17.4*18.7*4.8*1.0		5.0g	SUS304	Single sided	1.5-2.8	96
79	21.5*19.5*5.3*1.2		7.0g	65Mn	Single sided	1.0-3.0	240
80	21.7*21.5*8*1.6		10.0g	65Mn		1.8-4.8	240